


la belle Natura 2



la belle Natura 2



- Digital
- Module for glasses
- Fitting Software: SONIC innovations Expressfit
- For up to mild till hard of hearing loss
- Nine channels
- For all types of hearing loss
- Stabilised voltage switch
- Battery 312
- Option: telecoil
- Option: remote control
- Variants: mono, stereo, CROS, BiCROS
- Colours: gold-brown, silver-black, anthracite-black



TECHNICAL DATA

		DIN EN 60118-0	DIN EN 60118-7
Maximum sound output level SPL L_{Amax}	(dB)	127	115
Acoustical gain	(dB)	47	45
Equivalent input noise	(dB)	<25	<25
frequency range	(Hz)	200-5400	200-5400
Harm. distortionr 500 Hz	%	<6	<6
Harm. distortion 800 Hz	%	<4	<4
Harm. distortion 1600 Hz	%	<3	<3
Current	(mA)	1.5	
Attack time	(ms,2kHz)	5	5
Delay time	(ms,2kHz)	10	10

please turn over



Programming:

Expressfit with special Sonic Innovations-cable and adapter, recognised as ITC-P

Technical change without prior notice