


# freestyle CL 210



## freestyle CL 210




- modern communication system
  - 3 programmes selected by push button
  - 2-channel WDRC
  - Dynamic Contrast Detection
  - 12-band gain adjustment
  - MPO
  - adaptive feedback cancellation (until -17dB)
  - programme tones and battery tones
  - battery type 312
  - tube warm bendable
  - replaceable cerumen defender filter
  - can be adjusted to fit any individual ear shape
  - natural sound transfer quality via ex-speaker system\*
  - replaceable type ex-speaker cerumen defender filter
  - colours: titanium/transparent
- \* ex-speaker = speaker direct in the ear channel



## Technical data

		DIN EN 60118-0	DIN EN 60118-7
Max sound outputlevel OSPL90	(dB)	119	110
Acoustical gain max. 50dB(FOG)	(dB)	49	42
Equivalent input noise	(dB)	22	22
Frequency range	(Hz)	200-6000	250-6500
Operating current	(mA)	1,2	1,2

please turn over



Before programming, please remove the device cover plate

Programming:  
with Bruckhoff fitting software and Siemens programming cable (CONNEXX cable grey)

Technical change without prior notice