


freestyle CL 410



freestyle CL 410




- modern communication system
 - 4 programmes selected by push button
 - 4-channel WDRC
 - Dynamic Contrast Detection
 - 12-band gain adjustment
 - MPO
 - adaptive feedback cancellation (until -22dB)
 - layered noise reduction
 - programme tones and battery tones
 - battery type 312
 - tube warm bendable
 - replaceable cerumen defender filter
 - can be adjusted to fit any individual ear shape
 - natural sound transfer quality via ex-speaker system*
 - replaceable type ex-speaker cerumen defender filter
 - colours: titanium/transparent
- * ex-speaker = speaker direct in the ear channel



Technical data

		DIN EN 60118-0	DIN EN 60118-7
Max sound output level OSPL90	(dB)	119	112
Acoustical gain max. 50dB(FOG)	(dB)	52	43
Equivalent input noise	(dB)	22	22
Frequency range	(Hz)	200-6000	250-6500
Operating current	(mA)	1,2	1,2

please turn over



Before programming, please remove the device cover plate

Programming:
with Bruckhoff fitting software and Siemens programming cable (CONNEXX cable grey)

Technical change without prior notice